


INSTRUCTION MANUAL



Electric Intelligent Lifting Dressing Table
(TSZ/No cabinet)

USER MANUAL

Safe Use Instructions

- 1.The company shall not provide after-sales service for faults caused by modifying the product.
- 2.Do not replace the original adapted power supply to avoid short circuit and burning of the product.
- 3.Do not rinse the whole product with water to avoid short-circuit failure.
- 4.Do not forcefully block the cabinet door during lifting and lowering to avoid damaging the components;
- 5.To test the machine, please first remove the rubber slider of the guide rail before operation.
- 6.Please keep the guide rail straight and not deformed during installation to avoid affecting lifting;
- 7.This product is heavy and contains glass. Please install it with the cooperation of a companion;
- 8.Use the product in accordance with the instructions in this manual and do not operate it blindly;



Installation Video

Basic Parameters

Input Voltage: 100-240V

Output Voltage: 12V

Rated Power: 60W

Cabinet width dimension: 900/1000/1200mm

Cabinet height dimension: 750mm

Descending stroke: 550mm


Material: Aluminum alloy+Mirror+Board

Light color temperature: 4000K

Descent Time: 8s

Fatigue Test: 30,000 times

kfi-Collision Function: Yes



After-sales Warranty Card & Troubleshooting Guide

Common Failures and Causes Analysis

Solutions


- No response upon startup/No power ————— Socket energized
- Running light off/adaptor protection ————— The slide rail has no foreign matter
- The bottom protrudes a lot when lifted up ————— Adjusting the cabinet size

Warranty Regulations:

- 1. Warranty Period: 5 years (from the date of purchase)
- 2. Warranty scope: electrical system and motor parts and accessories.
- 3. Damage or destruction of parts caused by non-compliance with the operating instructions will not be warranted.
- 4. Unauthorized modification or replacement of other brands of parts, resulting in motor burnout will not be warranted.

Users information	Product information	Purchase Date	Warranty Records
Name:	Size:	_Y _M _D	Warranty 01
Name:	Size:	_Y _M _D	Warranty 02
Name:	Size:	_Y _M _D	Warranty 03
Name:	Size:	_Y _M _D	Warranty 04


Product Component Diagram



NO.	①	②	③	④	⑤
Name	Dressing Table Body	Adapter	Power Cable	Self-tapping Screw	User Manual
Pcs	1	1	1	1	1


Installation Instructions

1. Loosen the 2 screws on the front of the top of the chassis, and open the chassis panel.



Loosen the front screws



2. Push the Dressing Table up from the cabinet bottom opening to the top plate and lock screws.





Secure the screws on the top of the chassis

Installation Instructions

3. Power on, touch bottom switch, wait for Dressing Table to lower fully.




4. Lock 12 screws on left/right slide rail corners and panel, test Cloud Dressing Table operation.



Cabinet Size Parameters

TSZ dressing table 1200 external width cabinet dimension drawing; other dimensions can refer to the figure below.



Internal width of the cabinet(W)	Internal height of the cabinet(H)	Opening size(D)	Reserved height for descent(F)	Power cord hole
W=864	H=714MM	$\geq 195\text{MM}$	$\geq 600\text{MM}$	$\phi 20\text{MM}$
W=964	H=714MM	$\geq 195\text{MM}$	$\geq 600\text{MM}$	$\phi 20\text{MM}$
W=1164	H=714MM	$\geq 195\text{MM}$	$\geq 600\text{MM}$	$\phi 20\text{MM}$